

Han 24M-gs-M40



Image is for illustration purposes only. Please refer to product description.

| | |
|--------------------|---------------------------------------------------------------------------------------|
| Part number | 19 37 024 0528 |
| Specification | Han 24M-gs-M40 |
| HARTING eCatalogue | https://b2b.harting.com/19370240528 |

Identification

| | |
|--------------------------|--------------------|
| Category | Hoods/Housings |
| Series of hoods/housings | Han [®] M |
| Type of hood/housing | Hood |
| Type | High construction |

Version

| | |
|----------------------|---------------------------------------|
| Size | 24 B |
| Version | Side entry |
| Cable entry | 1x M40 |
| Locking type | Double locking lever |
| Field of application | Hoods/housings for rough environments |

Technical characteristics

| | |
|----------------------------------------|------------------------------------------------|
| Limiting temperature | -40 ... +125 °C |
| Note on the limiting temperature | For use as a connector according to IEC 61984. |
| Degree of protection acc. to IEC 60529 | IP65 IP66 IP67 |
| Type rating acc. to UL 50 / UL 50E | 4 4X 12 |

Material properties

| | |
|-------------------------|--------------------|
| Material (hood/housing) | Aluminium die-cast |
|-------------------------|--------------------|



Pushing Performance
Since 1945

Material properties

| | |
|--------------------------------------|----------------------------|
| Surface (hood/housing) | Powder-coated |
| Colour (hood/housing) | RAL 9005 (jet black) |
| RoHS | compliant |
| ELV status | compliant |
| China RoHS | e |
| REACH Annex XVII substances | Not contained |
| REACH ANNEX XIV substances | Not contained |
| REACH SVHC substances | Not contained |
| California Proposition 65 substances | Yes |
| California Proposition 65 substances | Nickel |
| Fire protection on railway vehicles | EN 45545-2 (2020-08) |
| Requirement set with Hazard Levels | R1 (HL 1-3) R7 (HL 1-3) |

Specifications and approvals

| | |
|-----------|------------------------------------------------------------|
| UL / CSA | UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076 |
| CE | Yes |
| Approvals | DNV GL |

Commercial data

| | |
|--------------------------------|------------------------------------------|
| Packaging size | 1 |
| Net weight | 245.8 g |
| Country of origin | Germany |
| European customs tariff number | 85389099 |
| GTIN | 5713140128941 |
| eCl@ss | 27440202 Shell for industrial connectors |