

Product information

95 32 315 A

Cable Cutter

(ratchet action)

For steel wire armoured cables (SWA cable)



MM 🚳

- Cuts through steel wire armoured cables up to Ø 45 mm / 380 mm² (e.g. 4 x 95 mm²) using one or two-handed operation
- Simple handling due to low weight (800 g) and compact design (315 mm length) can also be used in confined areas
- Precision-ground blades and induction-hardened cutting edges cut smoothly and neatly without crushing
- Innovative high leverage three-stage ratchet-drive
- Support area for putting down the pliers when cutting
- Not suitable for cutting ACSR cable and wire rope!
- High-grade special tool steel, forged, multi stage oil-hardened



General	
Article No.	95 32 315 A
EAN	4003773078562
Pliers	black lacquered
Handles	with multi-component grips
Weight	800 g
Dimensions	315 x 140 x 30 mm
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details	
Cutting capacity copper cable, multiple- stranded	380 mm ²
Cutting capacity copper cable, multiple- stranded	Ø 45 mm
MCM	750

technical change and errors excepted



Precision-milled and induction-hardened cutting edge