



## Description

The 83-17548 allows you to clear out your desk surface, while providing an ergonomic working position. It is designed to use with 13" – 27" monitors. The weight capability is 8kg/17.6lbs for each arm. Full motion structure allows maximum flexibility - extends, tilt and swivel your monitor up to 90° left and right for easy viewing. Its ball-joint structure allows smooth, effortless rotating and positioning for any direction, making it easy to reduce glare and find the perfect viewing angle. You can also adjust the monitor vertically to a desired position. Besides, cable clip is included for organizing cables.

## Features

- Two mounting options both desk clamp and grommet are included
- 360° Rotary VESA plate for more viewing experience
- Freely adjusting height for an optimal ergonomic position
- Cable management keeps everything organized

## Specifications

Type	: Articulating Monitor Arm
Material	: Aluminium, Steel
Surface Finish	: Powder Coating
Colour	: Slate Black
Dimensions	: 726mm × 116mm × 900mm (28.6" × 4.6" × 35.4")
Installation	: Grommet, Clamp
Suggested Screen Size	: 13" – 27"
Screen Quantity	: 4
Monitor Weight Capacity (per screen)	: 8kg (17.6lbs)
VESA Compatible	: 75 × 75, 100 × 100
Tilt Range	: +45° to -45°
Swivel Range	: +90° to -90°
Screen Rotation	: +180° to -180°
Arm Full Extension	: 328mm (12.9")
Pole Height	: 800mm (31.5")
Suggested Desktop Thickness	: Clamp: 10mm to 88mm / Grommet: 10mm to 80mm
Quick Release VESA Plate	: No
Cable Management	: Yes
Anti-theft	: No
Instruction Manual Included	: Yes

