



Switch Mode
Technology

General



Overview

Ideal for applications requiring mains and battery monitoring with fault outputs in addition to battery deep discharge protection.

Features

- 13.8V dc output
- Full rated current to load + 0.5A battery charging
- Mains and battery monitoring
- 2x Volt free fault outputs
- Battery deep discharge protection
- Front and rear tamper protection
- 3 year warranty

Part Number	Amp Rating	Dimensions	Will Fit Battery Size
G13801BM-A	1.0	200 H x 230 W x 80 D	1 x 7Ah
G13801BM-B		330 H x 355 W x 80 D	1 x 17Ah
G13801BM-C		275 H x 330 W x 80 D	
G13802BM-A	2.0	200 H x 230 W x 80 D	1 x 7Ah
G13802BM-B		330 H x 355 W x 80 D	1 x 17Ah
G13802BM-C		275 H x 330 W x 80 D	
G13803BM-B	3.0	330 H x 355 W x 80 D	1 x 17Ah
G13803BM-C		275 H x 330 W x 80 D	
G13804BM-B	4.0	330 H x 355 W x 80 D	1 x 17Ah
G13804BM-C		275 H x 330 W x 80 D	
G13805BM-B	5.0	330 H x 355 W x 80 D	1 x 17Ah
G13805BM-C		275 H x 330 W x 80 D	
G13810BM-8-C	10.0	275 H x 330 W x 80 D	2x7Ah
G13810BM-8-R	10.0	410 H x 390 W x 80 D	2 x 17Ah
			Dimensions (LxWxH)
G13801BMU	1.0	Unboxed	152 x 106 x 52
G13802BMU	2.0		
G13803BMU	3.0		152 x 106 x 71
G13805BMU	5.0		

Some part numbers within this range may be subject to MOQs

