

collet chuck DIN 6343 185 E, round

ORION®

Execution:

- hardened and ground
- clamping bridge max. 0.1 mm of the nominal diameter
- concentricity
- \varnothing 1-10 mm \leq 20 μ m
- \varnothing 11-30 mm \leq 30 μ m
- \varnothing 31-60 mm \leq 40 μ m
- up to \varnothing 8 mm smooth bore, from \varnothing 9 mm with crosswise grooves



Art. no.	23354 370
Brand	ORION
Manufacturer Part Number	23354370
Outer diameter	84 mm
Diameter	66 mm
Length	110 mm
Clamping diameter	7 mm
Profile shape	Round and smooth
Diameter 2	66 mm
Gross Weight	1.483 kg
Product Group	2AE

EAN

4053625356263