

## Mini temperature data logger

Model testo 174 T



### Application:

Handy data logger with large display and measured data memory for 16,000 readings.

### Delivery:

Mini data logger testo 174T, 1-channel, including wall bracket, battery (2 x CR 2032 lithium) and calibration log



<b>Art. no.</b>	<b>46200 200</b>
<b>Brand</b>	TESTO
<b>Manufacturer Part Number</b>	0572 1560
<b>Model</b>	testo 174 T
<b>Min./max. temperature measuring range</b>	-30 to 70 °C
<b>Digit increment (measuring instrument for temperature)</b>	0.1 °C
<b>Accuracy temperature</b>	+/- 0,5°C at -30 to +70°C
<b>Number of ducts</b>	1 PCS
<b>Data transmission type</b>	USB
<b>Measuring rate</b>	1 measurements/min
<b>Measured value memory</b>	16000 measuring results
<b>Hazard analysis and critical control points according to HACCP</b>	HACCP compliant
<b>IP protection class</b>	IP 65
<b>Colour</b>	White
<b>Material of housing</b>	Plastic
<b>Length x width x height</b>	60 x 38 x 18.5 mm
<b>Min./max. operating temperature</b>	-30 to 70 °C
<b>Battery designation</b>	3V CR2032 Lithium
<b>Number of rechargeable batteries/batteries</b>	2 PCS
<b>Weight</b>	35 g
<b>Channel type</b>	Internal
<b>Gross Weight</b>	0.086 kg
<b>Product Group</b>	4CF

### EAN

4029547010798