

## YALE Yalehandy lever chain hoist

Small and light for low weight applications

Yale

### Application:

For tensioning, hoisting, pulling and tying down.

### Execution:

- Compact and robust sheet steel housing
- Galvanised load chain in line with DIN EN 818-7 (quality class T)
- Smooth-running free-chaining feature for rapid load attachment
- 360° rotating carrying hook
- Chain end made of shatter-proof plastic
- Automatic threaded mechanical brake

### Advantage:

- Low tare weight
- Requires low lifting power



<b>Art. no.</b>	<b>77157 005</b>
<b>Brand</b>	YALE
<b>Manufacturer Part Number</b>	02300018
<b>Model</b>	Yalehandy 250
<b>Load-carrying capacity</b>	250 kg
<b>Nominal chain thickness</b>	12 mm
<b>Chain diameter</b>	4 mm
<b>Stroke force at nominal load</b>	25 daN
<b>Length of lever</b>	160 mm
<b>Stroke height per lever revolution</b>	80 mm
<b>Lift height</b>	1500 mm
<b>Min. hook spacing</b>	240 mm
<b>Number of load chains</b>	1 PCS
<b>EN standard</b>	818-7
<b>Gross Weight</b>	2.450 kg
<b>Product Group</b>	7EE

### EAN

4025092075039