

3893

ORIGINAL | Lamps with metal bases



Product benefits

- Wide product range
- Reliable quality

Product features

- Original spare parts



Product datasheet

Technical data



Electrical data

Power input	4 W
Nominal voltage	12.0 V
Nominal wattage	4.00 W
Power input tolerance	±10 %
Test voltage	13.5 V

Photometrical data

Luminous flux	35 lm
Luminous flux tolerance	±20 %

Dimensions & weight



Length	27.4 mm
Diameter	8.8 mm
Product weight	1.86 g

Lifespan

Lifespan B3	600 h
Lifespan Tc	1200 h

Additional product data

Base (standard designation)	BA9s
-----------------------------	------

Certificates & standards

ECE category	T4W
Approval marks – approval	E1 approval

Product datasheet

Country specific categorizations

Order reference	3893-02B 4W 12V
------------------------	-----------------

Country specific information

Product code	METEL code	SEG-No.	STK number	UK Org
4050300647609	OSRA3893BLI2	-	4730333	-
4050300838489	OSRA3893	-	-	-

Product datasheet

Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Volume	Gross weight
4050300647609	3893	Blister 2	69 mm x 14 mm x 55 mm	0.05 dm ³	8.72 g
4008321140395	3893	Shipping carton box 20	137 mm x - x 81 mm	1.17 dm ³	132.33 g
4050300838489	3893	Unpacked 1	31 mm x 10 mm x 10 mm	0.00 dm ³	3.00 g
4050300525068	3893	Folding carton box 10	46 mm x 29 mm x 112 mm	0.15 dm ³	29.60 g
4008321095626	3893	Shipping carton box 50	148 mm x - x 55 mm	0.94 dm ³	177.50 g

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.