

PRODUCT SPECIFICATION

**Carl
Kammerling**
International

| | |
|-------------------------|---------------------------|
| Brand | Kasp |
| Product Range | Harsh environment padlock |
| Catalogue number | 135 |
| Date | 08/03/2007 |

Range Description


Harsh environment padlock

Features

- Plastic coated and chrome plated hardened steel shackle – extra strength and resistance to corrosion
- Plastic coated nickel plated laminated steel body – maximum resistance to corrosion
- Double bolted locking mechanism – extra strength to resist torsion and pull attack
- Keyhole cover – protects the mechanism from dirt and moisture
- Paracentric keyway – extra protection against manipulation
- Weather rating: 3

These padlocks are supplied display packed in sealed blisters or individually boxed

2 keys are supplied with each padlock



| Item Number | Item Description | EAN No | Commodity code | Carton Qty |
|-------------|--|---------------|----------------|------------|
| K13545 | Harsh environment padlock 58mm – boxed | 5013969902518 | 8301100000 | 6 |
| K13545D | Harsh environment padlock 58mm – display packed | 5013969901016 | 8301100000 | 6 |
| K13545L63D | Harsh environment padlock, long shackle – 58mm x 63 mm | 5013969244793 | 8301100000 | 6 |

| <p>Technical product information</p> | <p>Body – Laminated steel, nickel plated, plastic coated</p> <p>Shackle- Hardened steel, chrome plated and plastic coated</p> <p>Locking mechanism- Pin tumbler cylinder type, 5 pin cylinder, Brass pins</p> <p>Key differs- 2000</p> <p>Re-keyable – No</p> <p>Key retaining – No</p> <p>Security rating:</p> <table border="1" data-bbox="488 982 878 1157"> <thead> <tr> <th>Item</th> <th>Security rating</th> </tr> </thead> <tbody> <tr> <td>K13545</td> <td>7</td> </tr> <tr> <td>K13545D</td> <td>7</td> </tr> <tr> <td>K13545L63D</td> <td>7</td> </tr> </tbody> </table> <p>Shackle Dimensions:</p> <table border="1" data-bbox="488 1268 1118 1495"> <thead> <tr> <th rowspan="2">Dimensions mm</th> <th colspan="3">Shackle</th> </tr> <tr> <th>Dia</th> <th>Internal width</th> <th>Internal height</th> </tr> </thead> <tbody> <tr> <td>K13545</td> <td>12</td> <td>21</td> <td>22</td> </tr> <tr> <td>K13545D</td> <td>12</td> <td>21</td> <td>22</td> </tr> <tr> <td>K13545L63D</td> <td>12</td> <td>21</td> <td>63</td> </tr> </tbody> </table> <p>Use environment- Harsh outdoor use</p> <p>Recommended applications- Outdoor applications where there is a high risk that dirt or moisture would affect the operation of a normal padlock</p> | Item | Security rating | K13545 | 7 | K13545D | 7 | K13545L63D | 7 | Dimensions mm | Shackle | | | Dia | Internal width | Internal height | K13545 | 12 | 21 | 22 | K13545D | 12 | 21 | 22 | K13545L63D | 12 | 21 | 63 |
|--------------------------------------|---|----------------|-----------------|--------|---|---------|---|------------|---|---------------|---------|--|--|-----|----------------|-----------------|--------|----|----|----|---------|----|----|----|------------|----|----|----|
| Item | Security rating | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| K13545 | 7 | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| K13545D | 7 | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| K13545L63D | 7 | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| Dimensions mm | Shackle | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| | Dia | Internal width | Internal height | | | | | | | | | | | | | | | | | | | | | | | | | |
| K13545 | 12 | 21 | 22 | | | | | | | | | | | | | | | | | | | | | | | | | |
| K13545D | 12 | 21 | 22 | | | | | | | | | | | | | | | | | | | | | | | | | |
| K13545L63D | 12 | 21 | 63 | | | | | | | | | | | | | | | | | | | | | | | | | |
| Standards compliance | None applicable | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| User health and safety information | None applicable | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| RoHS/WEEE compliance | This product does not fall within the scope of RoHS or WEEE regulations | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| Material safety data | None applicable | | | | | | | | | | | | | | | | | | | | | | | | | | | |

| | |
|-------------------|---|
| Warranty | KASP padlocks are guaranteed against defects in manufacture and/or materials for 10 years Damage caused through inappropriate use or attempted break in is not covered |
| Country of origin | China |

Dimensional details

| Item | Product only | | | | Product on primary packaging | | | |
|------------|--------------|----------|-----------|--------------|------------------------------|----------|-----------|----------------|
| | Width mm | Depth mm | Height mm | Net weight g | Width mm | Depth mm | Height mm | Gross weight g |
| K13545 | 63 | 37 | 84 | 384 | 65 | 37 | 88 | 396 |
| K13545D | 63 | 37 | 84 | 384 | 115 | 40 | 175 | 403 |
| K13545L63D | 63 | 37 | 125 | 424 | 115 | 40 | 175 | 443 |

| Item | Shelf box (secondary packaging) | | | | Euro Pallet data Wi x Hi | |
|------------|---------------------------------|----------|-----------|----------------|-----------------------------|---------------------|
| | Width mm | Depth mm | Height mm | Gross weight g | No of cartons on base | Number of rows high |
| K13545 | 115 | 143 | 95 | 2460 | | |
| K13545D | 120 | 200 | 160 | 2490 | | |
| K13545L63D | | | | | | |

Packaging waste details

| Item | Primary Packaging | | | | Secondary packaging | | | |
|------------|-------------------|---------|--------|--------------|---------------------|-----|--------|-----|
| | Plastic g | Use | Card g | Use | Plastic g | Use | Card g | Use |
| K13545 | | | 12 | Box | | | 84 | Box |
| K13545D | 12 | Blister | 7 | Backing card | | | 72 | Box |
| K13545L63D | 12 | Blister | 7 | Backing card | | | | |