


# Pluggable Terminal Blocks

Clamp Terminal 5.08 mm Pitch



## FEATURES:

Polarised Mouldings

Withstand Voltage - AC1500V/1min

Pin/Terminal - Tin plated brass

Screw/Torque - M2.5 Steel, Nickel Plated 0.4Nm

Recommended PCB hole size  $\phi$ 1.7 mm

Guided pin alignment

cUL approved

## SPECIFICATION:

Pitch	5.08 mm
Gender housing	Female
Termination type	Clamp Terminals/Screw Connection
Connection cross-section	0.33-2 mm <sup>2</sup> (22-14AWG)
Colour	green
Rated voltage to EN	300 V
Rated current to EN	15 A
Rated voltage to UL	300 V
Rated current to UL	15 A
Temperature range	-40...+105 °C

## PRODUCT RANGE:

Art. no.	Pole no.
RND 205-00177	2
RND 205-00178	3
RND 205-00179	4
RND 205-00180	5
RND 205-00181	6
RND 205-00183	8
RND 205-00184	9