

A Series 16 A 600 VAC

3 or 4 Contacts + Ground: 10A
 10, 16 & 32 Contacts + Ground: 16A



Use small blade screwdriver to push wire entry tab in for easy contact removal



Crimp Tool

Cat. No.

WT611TB

3 or 4 (600 V)	10	16	32
Install to Matching Series Hood/Base			

	3 or 4 + G	10 + G	16 + G	32 + G	
Screw Terminal Inserts					
	Male – Pins 20–14 AWG (0.5–2.5 mm ²)	MS203A or MS204A (16 AWG max.)	MS210A	MS216A	MS216A+ MS232A
	Female – Sleeves 20–14 AWG (0.5–2.5 mm ²)	FS103A or FS104A (16 AWG max.)	FS110A	FS116A	FS116A+ FS132A

Bases — Standard Mount				# of Contacts + Ground Connection			
				3 or 4 (600 V)	10	16	32
Single Lever	Double Lever	Housing	NPT Entry (in.)	Lever Locking Type			
				Single	Single	Single	Double
		Panel Base (No Cover)		PB303A(P)†	PB310A	PB316A	PB132A
		Panel Base w/Cover		PB403A	PB410A	PB416A	
		Angled, (No Cover)		PB503A(P)†			
		Box Base (No Cover)	1 x 3/8 1 x 1/2 1 x 3/4 1 x 1 2 x 1/2 2 x 3/4 2 x 1	BB403APMv†	BB410Amv BB510Amv	BB416Amv BB516Amv	BB032Amv BB832A BB132Amv BB132A100
		Box Base w/Cover	1 x 1/2 2 x 1/2		BB610Amv BB710Amv	BB616Amv BB716Amv	
Hoods — Standard Mount *Plastic body — “A” 3-16 Series standard Hoods include gaskets; Bases and Special Hoods do not							
		Side Entry	1 x 3/8 1 x 1/2 1 x 3/4 1 x 1	SH603APmv†	SH610Amv** SH710Amv**	SH616Amv** SH716Amv**	SH032Amv SH132Amv
		Top Entry	1 x 3/8 1 x 1/2 1 x 3/4 1 x 1	TH803APmv†	TH810Amv** TH910Amv**	TH816Amv** TH916Amv**	TH232Amv TH332Amv
Coupler Hoods — Inline For inline, portable or special service connections. Coupler Hoods mate to Standard Hoods ONLY.							
		Top Entry	1 x 3/8 1 x 1/2	CH803APmv†	CH810Amv	CH816Amv	
Lever Hoods — Reverse Locking Lever Hoods mate to Post Bases ONLY							
		Side Entry w/Lever(s)	1 x 3/4 1 x 1				LH032Amv LH132Amv
		Top Entry w/Lever(s)	1 x 3/4 1 x 1				LH232Amv LH332Amv
Bases — with Access Cover Post Bases accept Lever Hoods ONLY							
		Panel Base+ Posts w/Cover					PB232A
		Box Base+ Posts w/Cover	1 x 3/4 1 x 1 2 x 3/4 2 x 1				BB232Amv BB232A100mv BB332A BB332A100

** Low “L” profile may be available. Contact your Thomas & Betts sales representative.

† Indicates Thermoplastique renforcé de fibre de verre construction, light grey colour (add suffix)

* Indicates Thermoplastique renforcé de fibre de verre construction, black colour (add suffix); quantity purchase may be required