




SENKKOPF (100°) MIT GERILLEM NIETDORN COUNTERSUNK HEAD (100°) WITH GROOVED MANDREL TÊTE FRAISÉE (100°) CLOU CANNELÉ











Edelstahl A2 [1.4301]
Stainless steel A2 [AISI 304]
Acier inox A2 [1.4301]


Edelstahl A2 [1.4301]
Stainless steel A2 [AISI 304]
Acier inox A2 [1.4301]









Ø 4,8 mm

D1 = 4,8 +/- 0,09 mm
D2 = 9,0 + 0 / - 1,0 mm
k = 2,2 +/- 0,25 mm
d = 3,0 mm (Ref.)
P = ≥ 27,0 mm
L = +/- 0,99 mm
 4,9 - 5,1 mm

	F max							
4,8 x 13,0 mm	20,0 mm	4,5 - 8,4 mm	77715 04813	5700 N	4400 N	445 N	250	2500
4,8 x 17,0 mm	27,0 mm	7,7 - 12,7 mm	77715 04817				250	2500

Ø 6,4 mm

D1 = 6,4 + 0 / - 0,11 mm
D2 = 10,5 + 0 / - 1,5 mm
k = 2,4 +/- 0,4 mm
d = 4,0 mm (Ref.)
P = ≥ 31,0 mm
L = +/- 0,99 mm
 6,6 - 6,9 mm

	F max							
6,4 x 17,0 mm	27,0 mm	4,5 - 12,1 mm	77715 06417	10500 N	8200 N	1112 N	250	2500
6,4 x 23,5 mm	37,0 mm	10,5 - 17,0 mm	77715 06423				250	2500

¹⁾ typische Werte typical values valeurs moyennes

Technische Änderungen vorbehalten Subject to technical modifications Sous réserve de modifications (techniques)