

## Accessory

PICO-LPG-750-1100  
Order Number: 70149166

| Main Parameters (*)   | min | typ | max | Unit |
|-----------------------|-----|-----|-----|------|
| Operating Temperature | -50 |     | 85  | °C   |
| Storage Temperature   | -50 |     | 80  | °C   |

### Technical Parameters

RoHS yes

### Optical Parameters

|                        |  |
|------------------------|--|
| Luminous transmittance | 37.00 %  |
| LB Rating              | 180-315 D LB7 + IR LB4<br>750-800 + >1100-1120 DIR LB6<br>+ M LB6Y<br>>800-1100 D LB6 + IR LB7 + M<br>LB7Y |
| Lens Color             | Grün   |

### Mechanical Parameters

|               |               |
|---------------|---------------|
| Size          | 144x145x50 mm |
| Material      | Polymer       |
| Housing Color | black         |
| Weight        | 10 g          |

(\*) Over the complete operating temperature range

## Features




- Complete protection
- Comfortable fit over prescription glasses or alone
- Adjustable temples and Side-shields for wide field of view
- CE Certified EN 207
- With Picotronic Logo imprint

## Picture



## Safety Label



## Valid Revision

| 12-FEB-2021