



P.V.C. SLEEVING

P.V.C sleeving is supplied in a wide size range and in eleven colours. In addition to the three grades shown below we can offer material to BS3858, Type 3, which has a thinner wall, and general purpose sleeving which is useful where cost savings are required.

	Ref. C - GP	Ref. X - 85 T	Ref. Y - 105T
Continuous temperature	-20 to 70 C	-20 to 85 C	-40 to 105 C
Insulation resistance	10 ¹⁰ Ohm/cm	10 ¹⁰ Ohm/cm	10 ¹⁰ Ohm/cm
Dielectric strength	20 kV/mm	20 kV/mm	25 kV/mm
Tensile strength	15 MPa	15 MPa	18 MPa
Elongation at break	220%	220%	250%
Hardness	BSS20-30	BSS20-30	BSS25-35
Flammability	self extinguishing in 30 seconds		
Specification	N.A.	BS2848/3/85T	BS2848/3/105T
RoHS compliant	Yes	Yes	Yes

Part no. ref C - GP	Part no. ref. X - 85T	Part no. ref. Y - 105T	Inside dia. mm	Nominal wall mm	Coil size m
C 1	X 1	Y 1	1.0	0.5	100
C 1.5	X 1.5	Y 1.5	1.5	0.5	100
C 2	X 2	Y 2	2.0	0.5	100
C 3	X 3	Y 3	3.0	0.5	100
C 4	X 4	Y 4	4.0	0.5	100
C 5	X 5	Y 5	5.0	0.5	100
C 6	X 6	Y 6	6.0	0.5	100
C 7	X 7	Y 7	7.0	0.5	100
C 8	X 8	Y 8	8.0	0.5	100
C 9	X 9	Y 9	9.0	0.5	100
C 10	X 10	Y 10	10.0	0.5	100
C 12	X 12	Y 12	12.0	0.5	100
C 15	X 15	Y 15	15.0	0.5	100
C 20	X 20	Y 20	20.0	0.5	100
C 25	X 25	Y 25	25.0	0.5	50

Can be supplied in alternative wall thickness or on reels to special order.

Standard colours - black, yellow, red, blue, white, brown, green, violet, grey, orange, pink.

Clear available in C range only.

MORE INFO:

info@nedelko.nl

+31 (0)180 64 54 00