

Avide LED Flood Light Slim SMD 2x20W NW 4000K 2 head with Tripod

Product code: ABSFLNW-20W-TRIPOD-D
Brand link: avidelighting.com/qr/ABSFLNW-20W-TRIPOD-D
ID: AB-190518
Company name: Armin Trade Kft.
Company address: Kossuth utca 22 2/4, 4024 Debrecen



Date of issue: 2023-09-19

Page: 1/3

SPECIFICATIONS

EAN code: 5999097926322
Warranty: 3year(s)
Working temperature: -20 - +40 °C
Packaging: 1/b 4/c 80/p
Certifications:

BOX PICTURE

TECHNICAL DETAILS

Wattage: 40W
Voltage: 220-240V
Beam angle: 120°
Dimmability: No
Lumen output: 4 000lm
Color temperature: 4 000K
Lifetime: 25 000h
Energy class: F
Type of LED: SMD
Driver:
CRI: 80
IP standard: IP65



Avide LED Flood Light Slim SMD 2x20W NW 4000K 2 head with Tripod

Product code: ABSFLNW-20W-TRIPOD-D
Brand link: avidelighting.com/qr/ABSFLNW-20W-TRIPOD-D
ID: AB-190518
Company name: Armin Trade Kft.
Company address: Kossuth utca 22 2/4, 4024 Debrecen



Date of issue: 2023-09-19

Page: 2/3

PRODUCT SIZE

Width: 850mm
 Height: 1 645mm
 Depth: 850mm

CARDBOARD BOX

EAN: 5999097926322
 Packaging: 1/b 4/c 80/p
 Dimensions: 165mm x 640mm x 115mm
 Net weight: 2 900g
 Gross weight: 2 900g

CARTON

EAN: 5999097926339
 Packaging: 1/b 4/c 80/p
 Dimensions: 650mm x 335mm x 250mm
 Net weight: 11.6kg
 Gross weight: 11.6kg


PALLET EXAMPLE

Height:
 Width: 120cm (std Euro pallet)
 Mepth: 80cm (std Euro pallet)
 Cartons per pallet: 20carton/pallet
 Cartons per row:
 Net weight: 232kg
 Gross weight: 232kg

PRODUCT PICTURE



PRODUCT OUTLINE



Avide LED Flood Light Slim SMD 2x20W NW 4000K 2 head with Tripod

Product code: ABSFLNW-20W-TRIPOD-D
Brand link: avidelighting.com/qr/ABSFLNW-20W-TRIPOD-D
ID: AB-190518
Company name: Armin Trade Kft.
Company address: Kossuth utca 22 2/4, 4024 Debrecen



QR code:
Date of issue: 2023-09-19

Page: 3/3

PRODUCT DESCRIPTION

To ensure a more versatile use for Avide Floodlights our product range also features tripod stands. Our stands are available in single and double versions. Their height is 1 meter and 60 cm and they have a carrying capacity of 20 kilograms.