



Product Information

Product Category	REFRIGERATION
Unit Barcode	5016368062432
Outer Carton Barcode	
Commodity Code	8418219190
Country of Origin	CHINA
Primary Colour	WHITE
Finish	PAINTED STEEL
Primary Material	STAINLESS STEEL
Warranty	2
Self Assembly	NO
Perishable Item	NO
Hazardous Item	NO

General Product Specification

Voltage	230
Frequency	50
Wattage	80
Rated Current	0.45
Fuse Rating	13
Plug Type	BS 1363
Cable Diameter	0.75
Cable Length	1.6
Class	CLASS I
Conformity Markings	CE+UKCA

Packaging & Shipping Information

Product Dimensions H x W x D (mm)	840	480	500
Packaged Dimensions H x W x D (mm)	899	523	538
Outer Carton Dimensions H x W x D (mm)			
Outer Carton Qty.			
Unit Weight (Kg)			22
Unit Packaged Weight (Kg)			24
Carton Weight (Kg)			
EPS (Kg)	0.106	PPT Exempt Plastic (Kg)	
Other Plastic (Kg)	0.118	Card / Paper (Kg)	0.995
Aluminium (Kg)		Steel (Kg)	0.015

Category Specific Technical Information

Type	OTHER REFRIGERATING APPLIANCE	Number of Freezer Compartments	1
Design Type	FREESTANDING	Number of Fridge Shelves	1
Gross Total Volume		Door Hinge Position	
Net Total Volume	81	Reversible Door	YES
Net Refrigeration Volume	70	Door Handle Colour	WHITE
Net Freezing Volume	11	Door Handle Material	ABS
Energy Efficiency Index	125	Door Material	METAL
Energy Rating	F	Door Opening Angle	135
Airborne Acoustical Noise Emission Class		Housing Colour	WHITE
Annual Energy Consumption	169	Lamp Rated Power	
Climate Class	N	LED Lighting	YES
Minimum Ambient Operating Temperature	16	Power Failure Safe Storage	
Maximum Ambient Operating Temperature	32	Temperature Rise Time	5
Winter Setting	NO	Thermostat Temperature Range	-26
Freezer Star Rating	3	Thermostat Type	MECHANICAL
Fast Freeze Facility	NO	Refrigerant Type	R600A
Freezing Capacity		Refrigerant Amount	18
Defrosting Type	M	RF: Back Panel Material	FULL METAL
Freezer Technology	STATIC		