



FLAT BASE TOTE BOXES 21-701-XXXX

Wez standard containers are designed for euro pallets 1200x800 or 1200x1000.

Product specifications :

Material :	Conductive polypropylene (carbon-loaded)
Colour :	Black
ESD Marking :	All containers marked with ESD sign
Surface resistance :	$\leq 10e4$ Ohm
Usage temperature :	80°C. Please note that depending of load, deformation can appear from 50°C.
Stackability :	All containers may be stacked together in a wide range of configurations.
Average stack load :	500 kg
Standard compliance :	IEC 61340-5-1 / RoHS Directive (2002/95/CE)

Features & partnumbers :

Reference	Ext. Dim. (mm)	Int. Dim. (mm)	Usable depth (mm)	Capacity (litre)	Weight (gram)
21-701-0000	200x150x145	155x106x142	129	2.7	375
21-701-0010	300x200x100	254x154x96	83	3.75	520
21-701-0015	300x200x145	254x154x141	128	5.5	720
21-701-0020	400x300x53	354x254x49	40	4.4	540
21-701-0025	400x300x100	354x254x96	83	8.7	1030
21-701-0030	400x300x145	354x254x141	128	12.8	1200
21-701-0035	400x300x212	354x254x208	195	19.2	1610
21-701-0040	400x300x278	354x254x274	261	25.2	1975
21-701-0045	400x300x320	354x254x316	303	29.0	2100
21-701-0055	600x400x100	554x354x96	83	19.0	1650
21-701-0060	600x400x145	554x354x141	128	28.0	2050
21-701-0065	600x400x212	554x354x208	195	41.0	2550
21-701-0070	600x400x278	554x354x273	260	55.0	3070
21-701-0075	600x400x320	554x354x316	303	62.0	3400
21-701-0080	600x400x412	554x354x407	393	82.0	4605
21-700-0100*	400x300x145	354x254x141	128	12.8	700
21-700-0105*	600x400x145	554x354x141	128	28.0	1230

* light version : between 40% and 60% than the 'standard' container of the same size.



BACS A FOND PLAT 21-701-xxxx

La gamme standard des containers Wez est conçue pour les euro palettes 1200x800 ou 1200x1000.

Specification produit :

Matière :	Polypropylène conducteur (chargé carbone)
Couleur :	Noir
Marquage ESD:	Tous les bacs sont marqués du logo ESD
Résistance de surface :	≤ 10e4 Ohm
Température d'utilisation :	80°C. En fonction de la charge, des déformations peuvent apparaître dès 50°C.
Gerbabilité :	Tous les bacs peuvent être gercés ensemble avec une grande variété de combinaisons.
Capacité de gerbage :	500 kg
Conformité aux normes :	EN 61340-5-1 / Directive RoHS 2002/95/CE.

Caractéristiques et références :

Références	Dim. Ext. (mm)	Int. Dim. (mm)	Profondeur utile (mm)	Capacité (litre)	Poids (gram)
21-701-0000	200x150x145	155x106x142	129	2.7	375
21-701-0010	300x200x100	254x154x96	83	3.75	520
21-701-0015	300x200x145	254x154x141	128	5.5	720
21-701-0020	400x300x53	354x254x49	40	4.4	540
21-701-0025	400x300x100	354x254x96	83	8.7	1030
21-701-0030	400x300x145	354x254x141	128	12.8	1200
21-701-0035	400x300x212	354x254x208	195	19.2	1610
21-701-0040	400x300x278	354x254x274	261	25.2	1975
21-701-0045	400x300x320	354x254x316	303	29.0	2100
21-701-0055	600x400x100	554x354x96	83	19.0	1650
21-701-0060	600x400x145	554x354x141	128	28.0	2050
21-701-0065	600x400x212	554x354x208	195	41.0	2550
21-701-0070	600x400x278	554x354x273	260	55.0	3070
21-701-0075	600x400x320	554x354x316	303	62.0	3400
21-701-0080	600x400x412	554x354x407	393	82.0	4605
21-700-0100*	400x300x145	354x254x141	128	12.8	700
21-700-0105*	600x400x145	554x354x141	128	28.0	1230

* Version allégée : entre 40% et 60% plus léger que le bac 'standard' correspondant