

PRODUCT SPECIFICATION

Brand	C.K
Product Range	Pipe cutters
Catalogue number	2231 & 2232
Date	27/03/2014

Range Description

Pipe cutters

Features

T2231

- Adjustable pipe cutter for copper, brass, Aluminium and thin walled steel pipe
- Capacity 3 – 30mm diameter
- Easy grip handle with integral de-burring blade
- Replaceable hardened steel cutting blade for long life performance
- Black die cast lacquered body for strength and corrosion resistance

T2231A

- Adjustable pipe cutter for copper, brass, Aluminium and thin walled steel pipe
- Capacity 3 – 30mm diameter
- Easy grip handle
- New longer life 'easy glide' steel insert body threads
- Replaceable hardened steel cutting blade for long life performance – No tools required for convenience
- Black die cast lacquered body for strength and corrosion resistance



T2231



T2231A

T2232

- Compact adjustable mini pipe cutter for copper, brass, Aluminium and thin walled steel pipe
- Capacity 3 – 25mm diameter
- Replaceable hardened steel cutting blade for long life performance
- Black die cast lacquered body for strength and corrosion resistance

**T2232****T2232A**

- Compact adjustable mini pipe cutter for copper, brass, Aluminium and thin walled steel pipe
- Capacity 3 – 25mm diameter
- New longer life 'easy glide' steel insert body threads
- Replaceable hardened steel cutting blade for long life performance – No tools required for convenience
- Black die cast lacquered body for strength and corrosion resistance

**T2231A**

Item Number	Item Description	EAN No	Commodity code	Carton Qty
T2231	Pipe cutter	5013969980202	82034000	5
T2231A	Pipe cutter	5013969980516	82034000	5
T2232	Mini pipe cutter	5013969941500	82034000	10
T2232A	Mini pipe cutter	5013969941517	82034000	10
T2235	Spare cutting wheel for T2231 & T2232		82034000	10

Technical product information	
Standards compliance	None applicable
User health and safety information	None applicable
RoHS/WEEE compliance	This product range does not fall within the scope of RoHS or WEEE regulations
Material safety data	None applicable
Warranty	C.K tools are guaranteed for life against imperfect materials or workmanship Normal wear of cutting edges is not covered under the terms of this warranty
Country of origin	Spain

Dimensional details

Item	Product only				Product on primary packaging			
	Width mm	Depth mm	Height mm	Net weight g	Width mm	Depth mm	Height mm	Gross weight g
T2231	53	38	150	306	70	38	220	317
T2231A	60	37	158	278	70	38	230	289
T2232	40	23	65	177	70	25	100	183
T2232A	41	22	70	144	70	25	105	150
T2235	20	4	20	5				

Item	Shelf box (secondary packaging)				Euro Pallet data Wi x Hi	
	Width mm	Depth mm	Height mm	Gross weight g	No of cartons on base	Number of rows high
T2231	72	228	140	1644		
T2231A	72	228	140	1793		
T2232	75	183	110	1871		
T2232A	75	183	110	1889		
T2235	75	20	140	63		

Packaging waste details

Item	Primary Packaging				Secondary packaging			
	Plastic g	Use	Card g	Use	Plastic g	Use	Card g	Use
T2231			11	Backing card			59	Box
T2231A			11	Backing card			59	Box
T2232			6	Backing card			41	Box
T2232A			6	Backing card			41	Box
T2235					3	Bag		