

AS-i Substructure Module

Mounting on DIN rail and rear panel

for connection of AS-i flat cables:


- quick mounting technology for AS-i flat cable
- 2 AS-i flat cables (BW1180)
- 2 AS-i flat cables with addressing jack (BW1438)
- 1 AS-i flat cable,
1 flat cable for external power supply (BW1181)
- 1 AS-i flat cable,
1 flat cable for external power supply with addressing jack (BW1439)

for connection of AS-i round cables:

- screw terminal
- 2 AS-i round cables (BW1182)
- 1 AS-i round cable,
1 round cable for external power supply (BW1183)

Lid for standard AS-i substructure modules (BW1946)

AS-i ribbon cable seal for PG11 fittings (BW1945)



Article no. BW1180 for connection of 2 AS-i flat cables

Article no. BW1438 for connection of 2 AS-i flat cables with addressing socket

Article no. BW1439 for connection of 1 AS-i flat cable, 1 flat cable for external auxiliary power with addressing jack

Article no. BW1181 for connection of 1 AS-i flat cable, 1 flat cable for external power supply

Article no. BW1182 for connection of 2 AS-i round cables

Article no. BW1183 for connection of 1 AS-i round cable, 1 round cable for external power supply

Article no. BW1946 lid for standard AS-i substructure modules

Article no. BW1945 ribbon seal for PG11 fittings

AS-i substructure modules are some necessary accessories for AS-i modules of the product family IP65 M12- and IP65 PG-modules. They are available in versions for connection of AS-i flat and round cables.

With the use of the lid for standard AS-i modules further passive branches can be built up.

AS-i ribbon cable seal is used for packing of PG11 fittings for AS-i flat cable.

Article no.	BW1180	BW1438	BW1181	BW1439	BW1182	BW1183	BW1946	BW1945
Cable	2 AS-i flat cables		1 AS-i flat cable		2 AS-i round cables		-	
Gauge	-		-		< 2,5 mm ²		-	
Connection	contact pins in the unit				terminals up to 2,5 mm ²		-	
Contact rating	< 2 A				< 4 A		-	
Operating voltage	AS-i		AS-i/U AUX		AS-i	AS-i/U AUX	-	
Ambient operating temperature	-25 ... 75 °C							
Storage temperature	-25 ... 85 °C							
Protection category	IP65							
Dimensions (L / W / H in mm)	80 / 45 / 20				80 / 45 / 34		80 / 45 / 13	-
Packaging unit	1 piece							50 pieces