

EXHAUST FILTERS ROOF MOUNTED FAN CUT OUT
345X265 MM RAL 7035 DEGREE OF PROTECTION IP
44



Model		
product brand name		SIVACON
Product designation		outlet filter for roof mounting
Type of ventilation		ventilation
Fan design / Insertable fan		No
Design of the product / EMC version		No

General technical data		
Cutout width	mm	345
Cutout height	mm	265
Operating temperature / minimum	°C	-10

Protection class		
Protection class IP		IP54

Appearance		
Color		RAL 7035

Product details		
Product component / Fan		No

Mechanical Design		
Height	mm	340
Width	mm	420
Depth	mm	83
Installation location		Control cabinet roof
Mounting type		screw fixing
Mounting type		

- 19-inch installation
- wall mounting

No

No

Material

plastic

Certificates

Equipment marking

- acc. to DIN EN 61346-2
- acc. to DIN EN 81346-2

V

V

General Product Approval



Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://eb.automation.siemens.com/mall/en/WW/Catalog/Product/8MR60005DE40>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/8MR60005DE40/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mfb=8MR60005DE40

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://ausschreibungstexte.siemens.com/tiplv>

last modified:

11.03.2015