

Product information

70 06 140

Diagonal Cutter

DIN ISO 5749 IEC 60900 DIN EN 60900

- The indispensable diagonal cutter for all-round use
- High-quality material and precise workmanship for long service life
- Precision cutting edges for soft and hard wire
- Clean cutting of thin copper wires, also at the cutting edge tips
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 62 HRC
- Narrow head style for use in confined areas
- With bevel
- Vanadium electric steel, forged, multi stage oil-hardened



General

| | |
|-----------------|--|
| Article No. | 70 06 140 |
| EAN | 4003773040293 |
| Pliers | chrome-plated |
| Head | chrome-plated |
| Handles | insulated with multi-component grips, VDE-tested |
| Weight | 160 g |
| Dimensions | 140 x 54 x 25 mm |
| Standard | DIN ISO 5749 DIN EN 60900 IEC 60900 |
| REACH compliant | does not contain SVHC |
| RoHS compliant | not applicable |

Technical details

| | |
|--|----------|
| Cutting capacities soft wire (diameter) | Ø 4.0 mm |
| Cutting capacities medium hard wire (diameter) | Ø 2.5 mm |
| Cutting capacities hard wire (diameter) | Ø 1.8 mm |
| VDE tested | yes |

technical change and errors excepted

