

3-Wire Cordsets, Standard Plug Body

- NEMA 1, 3, 4, 6P
- IEC IP68 Protection
- 250 V, 4 A



Connector Style	Female Part Number	Male Part Number	Features	Pinout
<p>RK ..**</p>	RK 4T-*	RS 4T-*	AWM PVC Grey, 3x20 AWG, 105°C, 5.1 mm OD, Cable #RF50528-*M [†] , flexlife [®]	<p>Female</p> <p>1. BN 2. N/C 3. BU 4. BK</p> <p>Male</p>
	WK 4T-*	WS 4T-*		
<p>WK ..**</p>	RK 4T-*/S90	RS 4T-*/S90	AWM TPU Grey, 3x20 AWG, 90°C, 5.1 mm OD, Cable #RF50518-*M [†] , Cut/Abrasion Immune	
	WK 4T-*/S90	WS 4T-*/S90		
<p>RS ..**</p>	RK 4T-*/S101	RS 4T-*/S101	AWM TPE Grey, 3x20 AWG, 105°C, 5.7 mm OD, Cable #RF50940-*M [†] , flexLife-20, High Flex Over 20 Million Cycles	
	WK 4T-*/S101	WS 4T-*/S101		
<p>WS ..**</p>	RK 4T-*/S529	RS 4T-*/S529	TPU/Heavy Braid Double Jacket Yellow, 3x20 AWG, 90°C, 5.1 mm OD, Cable #RF50832-*M [†] , Cut/Abrasion Immune Braided Mechanical Shield	
	WK 4T-*/S529	WS 4T-*/S529		
<p>RS ..**</p>	RK 4T-*/S824	RS 4T-*/S824	PLTC AWM PVC Grey, 3x20 AWG, 105°C, 5.1 mm OD, Cable #RF50829-*M [†] , Tray Rated	
	WK 4T-*/S824	WS 4T-*/S824		
<p>WS ..**</p>	RK 4T-*/S715	RS 4T-*/S715	AWM PVC Yellow, 3x20 AWG, 105°C, 5.1 mm OD, Cable #RF50674-*M [†] , flexlife	
	WK 4T-*/S715	WS 4T-*/S715		
<p>WS ..**</p>	RK 4T-*/S760	RS 4T-*/S760	AWM PVC Black, 3x20 AWG, 105°C, 5.1 mm OD, Cable #RF50795-*M [†] , flexlife	
	WK 4T-*/S760	WS 4T-*/S760		
<p>WS ..**</p>	RK 4T-*/S618	RS 4T-*/S618	ITC/PLTC PVC Grey, 3x20 AWG, Foil/Drain, 105°C 5.7 mm OD, Cable #RF50611-*M [†] , RFI/EMI Shielding, tray rated	
	WK 4T-*/S618	WS 4T-*/S618		

* Length in meters. Standard cable lengths are 2, 4, 6, 8 and 10 meters. Consult factory for other lengths.

** Standard coupling nut material is nickel plated brass "RK .."; "RKK .." indicates nylon and "RKV .." indicates stainless steel.

† See Section N for **reelfast**® cable information.