

06.84.126	<b>Locking Circuit Board Support / Threaded Female</b>
Length	12,0 mm
Material	Nylon 66
Thread Typ	M4
Dia. Hole Board	4,0 mm
Dia. Hole Chassis	4,2 mm
Typ	Support Threaded Male
UL-Flamability	UL94 HB
Board Thickness	1,80 mm
Model	Support Treaded Female
Colour	black
Design	Look / Thread
	RoHS konform / WEEE konform / 76/769/EWG konform / PAKs frei

