

Ergonomic WG workbench with electric height adjustment

Solid beechwood 1500 mm, height-adjustable via a control panel

Version:

- Base made of square steel tube, outer 60 x 60 x 2 mm, inner 55 x 55 x 2 mm, with level compensation on all four feet
- Height infinitely adjustable from approx. 740-1040 mm via an electric control panel
- One perforated metal panel wall on both the right and left end faces of the workbench
- Fully assembled

Advantage:

- Workbench can be quickly and easily adjusted to the desired working height
- Always working at the right height ensures ideal ergonomic conditions
- Up to 4 different work heights are programmable and accessible at the touch of a button thanks to the memory function
- When you buy this product, you plant a tree and also receive a tree certificate!



Art. no.	50185 039
Material of worktop	Solid beech
Plate length	2000 mm
Panel depth	700 mm
Board thickness	50 mm
Min. height	740 mm
Max. height	1040 mm
Number of drawers	1 PCS
Drawer front height	1 x 180 mm
Draw width (inner dimension)	450 mm
Drawer depth (inner dimension)	600 mm
Pullout type	Full extension
Type	Electrical height adjustment
Load-carrying capacity per drawer	70 kg
Drawer surface	0.27 m ²
Material of base frame	Steel plate
With single pull-out safety brake	Yes
Adjustable in height	Yes
Levelling	Yes
Load-carrying capacity	800 kg
Dynamic load-carrying capacity	400 kg
Central locking	Yes
Functions	RFID possible
Body colour	Light grey RAL 7035
Colour of front	Anthracite grey RAL 7016
Surface	Powder-coated

EAN-Code

4053625402243