

LED light strips for machines and workstations

630 mm, 28.8 W, 3800 lm, IP 67, 230 V

ATORN®

Application

For lighting workbenches, cabinets, shelves, inside and outside machines or simply on the wall

Version

- High-performance brand LED, light colour temperature 5500 K (cold white), 140° beam angle
- Lamp housing made of anodised aluminium
- Resistant to liquids such as water, oils, coolants and cleaning agents
- Energy efficiency class A++
- Can be mounted using magnets or with two mounting brackets for precise alignment of the light beam.

Advantage

- For universal use
- The slim design means it fits easily into tight spaces and guarantees optimum illumination of the work surface.
- Made in Germany

Delivery

With rubber-coated strong adhesive magnets (2 pcs. /45 mm) and an additional two mounting brackets with screws for mounting



Art. No.	56869 100
Power rating	28.8 W
Length	630 mm
Luminous flux	3800 lm
IP protection class	IP 67

EAN-Code

405029366 1507