

LED lamp socket E27

Matt, dimmable or non-dimmable

Execution:

- Screw socket E27
- High-quality lamp with a very long service life of min. 15,000 hours
- Light colour temperature 2700 K
- Ra value 80, energy efficiency class A+ or A++
- Pear-shaped light fixture in frosted glass

Art. no.	56887 040
Dimmable	Yes
Luminous flux	806
Power rating	8.5
Gross Weight	0.120 kg
Product Group	5IH

EAN

8719514347861

