

CM 11 milliampere current clamp multimeter

Accurate measurement of small AC/DC currents with maximum resolution of 0.1 mA

BENNING

Application:

Ideal for troubleshooting problems in electrical installations, control systems, devices and motor vehicle electrical systems.

Delivery:

includes accessories: bag, batteries, measuring leads

Art. no.	75024 391
Brand	BENNING
Manufacturer Part Number	044067
Model	CM 11
Display range	6000 digits
Measuring accuracy	+/- 1 %
Min./max. test voltage (DC)	10 mV/DC-600 V/DC
Min./max. test voltage (AC)	10 mV/AC-600 V/AC
Min./max. alternating current of measuring range	100 µA-20 A/AC
Min./max. direct current of measuring range	100 µA-10 A/DC
Continuity testing	Yes
Diode testing	No
Min./max. electrical-resistance measuring range	0.1 Ohm-600 kOhm
Max. collet opening	23 mm
Memory function	HOLD, MAX/MIN
Measuring procedure	TRUE RMS
Overvoltage protection category	CAT IV/300 V, CAT III/600 V
Length x width x height	206 x 76 x 33 mm
Gross Weight	0.650 kg
Product Group	7AH



EAN

4014651440678