

Spring balances with load capacity of 0.5-3.0 kg, with automatic lock

Type 7212, cable extension 2500 mm, rustproof

AUTOSTAT

Execution:

- housing made of extremely impact-resistant special plastic
- Cable drum is made of non-abrasive plastic
- High-strength special motive spring
- Simple load setting secured against incorrect operation
- cable feed limitation is impact absorbing and adjustable
- the load is attached via a safe snap hook
- Suspension with screw snap hook
- Safety device: Fall arrester in line with DIN 15112 included in scope of delivery, insulated suspension, shape-stabilised structure
- Working area: Cable extraction: 1600-2500 mm, ropes in special lengths available on request
- The automatic cable retraction stop allows the device to be locked. Locking not to be used for load change!

Advantage:

- Effortless work



Art. no.	77001 587
Brand	AUTOSTAT
Manufacturer Part Number	77001587
Min. load-carrying capacity	1.5 kg
Max. load-carrying capacity	3 kg
Type	7212
With automatic locking	Yes
Max. cable pull-out length	2500 mm
Adjustable cord length	No
Material of cord	Stainless Steel
Wire cable diameter	2 mm
Replaceable cord	No
Cord in-feed restriction	Absorbs impacts, adjustable
Material of cable drum	Abrasion-proof plastic
Suspension type	Freely rotating and pivot screw karabiner hook
Load attachment	Screw Karabiner hook
Material of housing	Plastic
Housing height	166.5 mm
Housing width	133 mm
Housing thickness	45 mm
Design	All external components made of non-rusting material
Height	363 mm
Spring design	Special mainspring
With overrotation protection	No
Spring breakage protection	No
Number of springs	1 PCS
DIN	15112
Gross Weight	1.003 kg
Product Group	7EB

EAN

4053625360277