

Screw plug

10.xx15 M/G


Configuration

Screw plug	Brass CuZn39Pb3, nickel-plated
O-ring	Nitrile rubber
Connecting thread	metric, as per EN 60423




Properties

	<ul style="list-style-type: none"> for secure sealing of unused threaded or clearance hole
Temperature range	-30°C +100°C
Protection grade	IP65 / IP68 Type 4X
Test standard	UL 514A, 25 UL 50, 35.2 UL 746C, 14
UL / CSA-File	E140310



Features

A	L	H	Da		Part No.
	mm	mm	mm	Piece	
M12x1,0	4,5	7,5	16	100	10.1210 M/G
M12x1,5	5	8	16	100	10.1215 M/G
M16x1,5	6	9	20	100	10.1615 M/G
M20x1,5	6,5	9,5	24	100	10.2015 M/G
M25x1,5	7	11	28	100	10.2515 M/G
M32x1,5	8	12	35	50	10.3215 M/G
M40x1,5	8	12	45	50	10.4015 M/G
M50x1,5	9	15	55	25	10.5015 M/G
M63x1,5	10	16	68	10	10.6315 M/G