

## 53/1.2M boxes



Description	Specification	Pcs	Art. No.	EAN Code	Units
53/6 mm	Galvanized	1200	23807400	7313468074005	10
53/8 mm	Galvanized	1200	23808800	7313468088002	10
53/10 mm	Galvanized	1200	23808900	7313468089009	10
53/12 mm	Galvanized	1200	23809000	7313468090005	10
53/14 mm	Galvanized	1200	23807600	7313468076009	10




## 53/Narrow blisters



Description	Specification	Pcs	Art. No.	EAN Code	Units
53/4 mm	Galvanized	1620	40109501	3221631095013	5
53/6 mm	Galvanized	1080	40109502	3221631095020	5
53/8 mm	Galvanized	1080	40109503	3221631095037	5
53/10 mm	Galvanized	1080	40109504	3221631095044	5
53/12 mm	Galvanized	1080	40109505	3221631095051	5
53/14 mm	Galvanized	1080	40109506	3221631095068	5
53/20 mm	Galvanized	540	40109508	3221631095082	5
53/6 mm	Stainless steel	1080	40109509	3221631095099	5
53/8 mm	Stainless steel	1080	40109510	3221631095105	5
53/10 mm	Stainless steel	1080	40109511	3221631095112	5
53/12 mm	Stainless steel	1080	40109512	3221631095129	5
53/6mm	Galvanized	2130	5000741	4051661023095	5
53/8mm	Galvanized	2130	5000742	4051661023132	5
53/10mm	Galvanized	2130	5000743	4051661023170	5



## 4-in-1




Description	Specification	Pcs	Art. No.	EAN Code	Units
53/8/9/7	Galvanized	1740	40109414	3221631088718	10



### FOR LOW VOLTAGE CABLES

With their rounded crown, these flatwire staples are specifically designed for fastening low voltage cables up to 50 V such as computer, hi-fi speaker or telephone cables. Diverging points, DP, makes leg points go in opposite directions, for extra strong bonding.

## 28/5M boxes



Description	Specification	Pcs	Art. No.	EAN Code	Units
28/9 mm	Galvanized	5x1000	11890131	7313468901318	25
28/10 mm	Galvanized	5x1000	11893510	7313468935108	20
28/11 mm	Galvanized	5x1000	11891933	7313468919337	20
28/9 mm	White	5x1000	11890130	7313468901301	25
28/10 mm	White	5x1000	11893511	7313468935115	20
28/11 mm	White	5x1000	11891931	7313468919313	20



## 36/5M boxes



Description	Specification	Pcs	Art. No.	EAN Code	Units
36/10 mm	Superstrong - Galvanized	5x1000	5000774	4051661023552	20
36/12 mm	Superstrong - Galvanized	5x1000	5000511	4051661017360	20
36/14 mm	Superstrong - Galvanized	5x1000	5000512	4051661017377	15
36/10 mm	Galvanized	5x1000	11884410	7313468844103	20
36/12 mm	Galvanized	5x1000	11885110	7313468851101	20
36/14 mm	Galvanized	5x1000	11886910	7313468869106	15
36/10 mm	White	5x1000	11884431	7313468844318	20
36/14 mm	White	5x1000	11886911	7313468869113	15



## 36/Narrow blisters



Description	Specification	Pcs	Art. No.	EAN Code	Units
36/12 mm	Galvanized	864	40109626	3221631096263	5
36/14 mm	Galvanized	864	40109627	3221631096270	5



## 7/Narrow blisters



Description	Specification	Pcs	Art. No.	EAN Code	Units
7/12 mm	Galvanized	960	40109523	3221631095235	5
7/14 mm	Galvanized	960	40109524	3221631095242	5

