

# Marking Tag Number



## Features


- ROHS compliant
- Marker tags for use with wide range of DIN Rail terminal blocks
- Abrasion resistant printing
- Numbering: 1 to 50



## Specification


Colour	White
Insulating Body Material	PA66 (UL94-V0)
Length	4.9 mm
Width	5.9 mm
Height	2.6 mm
Operating Temperature	-40 ... 105 °C

## Drawing



Art.Nr.  
RND 205-01341

## RND Din-Rail Terminal Block Assortment



### Screw Clamp Terminal Block

#### Art Nr. - Wire Range, Colour

RND 205-01319 - 0.5 ... 2.5mm<sup>2</sup>, Grey  
RND 205-01320 - 0.5 ... 2.5mm<sup>2</sup>, Blue  
RND 205-01321 - 0.5 ... 2.5mm<sup>2</sup>, Orange  
RND 205-01322 - 0.5 ... 2.5mm<sup>2</sup>, Beige  
RND 205-01323 - 0.5 ... 2.5mm<sup>2</sup>, Red  
RND 205-01324 - 0.5 ... 2.5mm<sup>2</sup>, Black  
RND 205-01325 - 0.5 ... 4mm<sup>2</sup>, Grey  
RND 205-01326 - 0.5 ... 4mm<sup>2</sup>, Blue  
RND 205-01327 - 0.5 ... 6mm<sup>2</sup>, Grey  
RND 205-01328 - 0.5 ... 6mm<sup>2</sup>, Blue  
RND 205-01329 - 1.5 ... 10mm<sup>2</sup>, Grey  
RND 205-01330 - 1.5 ... 10mm<sup>2</sup>, Blue



### Ground Terminal Blocks

#### Art Nr. - Wire Range

RND 205-01331 - 0.5 ... 2.5mm<sup>2</sup>  
RND 205-01332 - 0.5 ... 4mm<sup>2</sup>  
RND 205-01333 - 0.5 ... 6mm<sup>2</sup>  
RND 205-01334 - 1.5 ... 10mm<sup>2</sup>