

# Fan CXT®

## CF101DZ

12V max • 4.6 m<sup>3</sup>/min

**Compact, efficient fan with three air flow settings and pendulum action**

A compact cordless portable fan with three air flow settings that fits in a small space. Brings added comfort in hot weather and speeds up drying of paint or filler. 45 degree pendulum action left and right. Includes a mains adapter. Tool only, battery and charger not included.



### ■ Technical specifications

CXT Battery	✓
Nominal Battery Voltage	12 V
Battery protection	✓
Max. Bevel Range (Left)	45 °
Max. Air Velocity	3,0 / 2,5 / 2,0 m/s
Air volume	4,6 / 3,8 / 3,0 m <sup>3</sup> /min
Operating time slow blow	630 min
Operating time middle blow	380 min
Operating time high blow	275 min
Tool weight with battery (EPTA)	1,3 - 1,7 kg
Diameter (D)	180 mm
Product Dimensions (L x W x H):	185 x 260 x 284 mm

### ■ User benefits

- Three speed settings (High/Medium/Low)

■ **EAN 0088381865005**

Link to product - [www.makita.com](http://www.makita.com)



# Related products

## ■ Other

User manual

Parts drawing