

AS-INTERFACE SAFETY AT WORK SLIMLINE S22.5F
STANDARD IP20 2F-DI



General technical data:		
Design of the product		Safe SlimLine module S22,5F, 2F-DI
Type		2 inputs, safe
I/O configuration		0
ID/ID2 code		B/F
Protocol is supported AS-interface protocol		Yes
Type of electrical connection of the inputs and outputs		screw terminal
operating voltage according to AS-Interface specification	V	26.5 ... 31.5
AS interface total current input max	mA	45
Addressing		front addressing socket
Equipment marking acc. to DIN 40719 extended according to IEC 204-2 acc. to IEC 750		A
Equipment marking acc. to DIN EN 61346-2		A
Inputs:		
Number of digital inputs safety-related		2
Inputs		mechanical switching contact contact closed contact open
Input current at digital input for signal <1> minimum	mA	5
Outputs:		
Type of voltage of output voltages		DC
Status display		

- display of I/Os
- display of AS-Interface/diagnostics

yellow LED
green/red LED

Ambient conditions:

Ambient temperature		
• during operation	°C	-25 ... +70
• during storage	°C	-40 ... +85
Protection class IP		IP20

Mechanical data:

Width	mm	22.5
Height	mm	90
Depth	mm	91
Mounting type		standard rail mounting/wall mounting

Certificates/ approvals:

AS-Interface certificate		yes
Approvals		UL, CSA

General Product Approval	Functional Safety/Safety of Machinery	Declaration of Conformity
---------------------------------	--	----------------------------------



[Type Examination Certificate](#)



Shipping Approval



other

[Confirmation](#)

[Environmental Confirmations](#)

[Declaration of Conformity](#)

[other](#)

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)


<http://www.siemens.com/industrial-controls/catalogs>

Industry Mall (Online ordering system)

<http://www.siemens.com/industrymall>

Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RK12050BE000AA2>



last modified:

09.03.2015