



4W

VT-706 4W LED WALL LIGHT COLORCODE:3000K IP65 BLACK BODY ROUND

Lumens <b>440</b>	Beam Angle <b>360</b>	Dimensions <b>150x50mm</b>
----------------------	--------------------------	-------------------------------

Warm White  
SKU:8215



## Technical Information

Instant Start: 0-100% in 11s	IP Rating: IP65
Watts: 4	Dimmable: No
Lumens: 440	Warranty (Years): 2
Shape: Round	PF: >0.5
Beam Angle: 360	CRI: >80
Unit Color: Black	Operation Temperature: -25 to +50°C
Body Type: Aluminium + Acrylic	Input Power: AC:220-240V,50/60Hz
Long life: 20,000 Hours	Sensor Compatibility: Yes

## Features

- ✓ Perfect choice for Interior and Exterior aesthetics
- ✓ Wall washer to create attractive beam designs
- ✓ High quality LED Chips for reliable lighting effect
- ✓ IP65 rated solid ingress protection
- ✓ Glass screen for controlled light beams
- ✓ Available in different color options - Warm White and Day White
- ✓ Applications - Outdoor, Façade, Residential, Restaurants, Building and many more

Note: 

Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

## Packaging

### Unit Details

Gross Weight(GW) Kgs	0.784
Length(Box)mm	160
Width(Box)mm	180
Height(Box)mm	55
Unit CBM	0.001584

### Listing Details

EAN Code	3800157623322
Commodity Code	9405403990

### Master Box Packaging

Master Box Qty (Pcs Per Carton)	20
Qty Per Pallet	720

READY STOCKS IN  
**UK & EU**



Dispatch within  
24 Hours

[www.vtacexports.com](http://www.vtacexports.com)

OUR PRODUCTS ARE  
CURRENTLY SOLD IN OVER  
**70**  
COUNTRIES