



**RoHS  
Compliant**



## Specifications

Material : Polyester, Glasfilled, Black (UL944-0)  
 Temperature Range : -55°C to +125°C  
 For Use With : MH105 Series IDC D-Sub Connectors

## Diagram



## Part Number Table

Description	Dim. "A"	No of Positions	D-Sub Shell Size	Part Number
Strain Relief	16.6mm	9	DE	MH-10175
	25mm	15	DA	MH-10176
	38.9mm	25	DB	MH-10177
	55mm	37	DC	MH-10178

Dimensions : Millimetres

**Important Notice** : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro  
 Farnell.com/multicomp-pro  
 Element14.com/multicomp-pro