

Han E Female Contact 20 Awg



Part number	09 33 000 6262
Specification	Han E Female Contact 20 Awg
HARTING eCatalogue	https://b2b.harting.com/09330006262

Image is for illustration purposes only. Please refer to product description.

Identification

Category	Contacts
Series	Han E [®]
Type of contact	Crimp contact

Version

Gender	Female
Contact identification	acc. to IEC 60584 type J
Manufacturing process	Turned contacts

Technical characteristics

Conductor cross-section	0.5 mm²
Conductor cross-section	AWG 20
Operating current	≤16 A
Contact resistance	≤1 mΩ
Stripping length	7.5 mm

Material properties

Material (contacts)	Constantan
RoHS	compliant
ELV status	compliant
China RoHS	е
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained

Page 1 / 2 | Creation date 2023-02-03 | Please note that the data specified here were taken as extracts from the online catalogue. Please refer to the user documentation for the complete and up-to-date information and data. Please also note that the user is responsible for validating functionality, conformity with applicable laws and directives, as well as for the electrical safety in the particular application.

HARTING Stiftung & Co. KG | Marienwerderstr. 3 | 32339 Espelkamp | Germany



Material properties

REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel

Specifications and approvals

Charifications	IEC 60664-1
Specifications	IEC 61984

Commercial data

Packaging size	25
Net weight	1.64 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140050105
eCl@ss	27440204 Contact for industrial connectors