



Notification																																																	
Product Code	USB3-VGAHRS																																																
Short Description	USB 3.0 - VGA Adaptor																																																
Full Description	<p>The USB 3.0 to VGA Adaptor allows the user to mirror or extend their current PC or laptop desktop across another monitor up to resolutions of 1600 x 1200 standard display and 2048 x 1152 widescreen display on VGA/SVGA monitors.</p> <table border="1"> <thead> <tr> <th>Wide Screen</th> <th>Colour Depth</th> <th>Standard Screen</th> <th>Colour Depth</th> </tr> </thead> <tbody> <tr> <td>2048 x 1152</td> <td>16, 32 bits</td> <td>1600 x 1200</td> <td>16, 32 bits</td> </tr> <tr> <td>1920 x 1200</td> <td>16, 32 bits</td> <td>1400 x 1050</td> <td>16, 32 bits</td> </tr> <tr> <td>1920 x 1080</td> <td>16, 32 bits</td> <td>1280 x 1024</td> <td>16, 32 bits</td> </tr> <tr> <td>1680 x 1050</td> <td>16, 32 bits</td> <td>1280 x 960</td> <td>16, 32 bits</td> </tr> <tr> <td>1600 x 900</td> <td>16, 32 bits</td> <td>1152 x 864</td> <td>16, 32 bits</td> </tr> <tr> <td>1440 x 900</td> <td>16, 32 bits</td> <td>1024 x 768</td> <td>16, 32 bits</td> </tr> <tr> <td>1366 x 768</td> <td>16, 32 bits</td> <td>800 x 600</td> <td>16, 32 bits</td> </tr> <tr> <td>1360 x 768</td> <td>16, 32 bits</td> <td></td> <td></td> </tr> <tr> <td>1280 x 800</td> <td>16, 32 bits</td> <td></td> <td></td> </tr> <tr> <td>1280 x 768</td> <td>16, 32 bits</td> <td></td> <td></td> </tr> <tr> <td>1280 x 720</td> <td>16, 32 bits</td> <td></td> <td></td> </tr> </tbody> </table>	Wide Screen	Colour Depth	Standard Screen	Colour Depth	2048 x 1152	16, 32 bits	1600 x 1200	16, 32 bits	1920 x 1200	16, 32 bits	1400 x 1050	16, 32 bits	1920 x 1080	16, 32 bits	1280 x 1024	16, 32 bits	1680 x 1050	16, 32 bits	1280 x 960	16, 32 bits	1600 x 900	16, 32 bits	1152 x 864	16, 32 bits	1440 x 900	16, 32 bits	1024 x 768	16, 32 bits	1366 x 768	16, 32 bits	800 x 600	16, 32 bits	1360 x 768	16, 32 bits			1280 x 800	16, 32 bits			1280 x 768	16, 32 bits			1280 x 720	16, 32 bits		
Wide Screen	Colour Depth	Standard Screen	Colour Depth																																														
2048 x 1152	16, 32 bits	1600 x 1200	16, 32 bits																																														
1920 x 1200	16, 32 bits	1400 x 1050	16, 32 bits																																														
1920 x 1080	16, 32 bits	1280 x 1024	16, 32 bits																																														
1680 x 1050	16, 32 bits	1280 x 960	16, 32 bits																																														
1600 x 900	16, 32 bits	1152 x 864	16, 32 bits																																														
1440 x 900	16, 32 bits	1024 x 768	16, 32 bits																																														
1366 x 768	16, 32 bits	800 x 600	16, 32 bits																																														
1360 x 768	16, 32 bits																																																
1280 x 800	16, 32 bits																																																
1280 x 768	16, 32 bits																																																
1280 x 720	16, 32 bits																																																
Extra Information	<p>Specification Compliant with USB 3.0 specification Mirror, Primary and Extended display modes Resolutions up to 1600 x 1200 standard display & 2048 x 1152 widescreen at 16, 32 bit Supports Windows XP, Win 7 and Mac Snow Leopard / Lion</p> <p>System Requirements 1 - 2 Adaptors: CPU: Intel Core i3 2.8GHz or same level RAM: 2GB or higher 3 - 4 Adaptors: CPU: Intel i5 Quad Core 2.8GHz or same level RAM: 4GB or higher 5 - 6 Adaptors: CPU: Intel i7 Quad Cor 3.0GHz or same level RAM: 8GB or higher</p>																																																