

## Han B Prot.Cover Die Cast for CtoC hood



Image is for illustration purposes only. Please refer to product description.

Part number	09 30 024 5436
Specification	Han B Prot.Cover Die Cast for CtoC hood
HARTING eCatalogue	<a href="https://b2b.harting.com/09300245436">https://b2b.harting.com/09300245436</a>

### Identification

Category	Accessories
Series of hoods/housings	Han <sup>®</sup> B
Type of accessory	Protection cover
Description of the accessory	for cable to cable housing Metal With fixing cord

### Version

Size	24 B
Locking type	Single locking lever

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4 4X 12

### Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained



**Pushing Performance**  
Since 1945

## Material properties

REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

## Specifications and approvals

Approvals	DNV GL
-----------	--------

## Commercial data

Packaging size	1
Net weight	79 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140048010
ETIM	EC002314
eCl@ss	27440208 Cap for industrial connectors