

Micromar 40 EWri-V electronic micrometer set

with sliding spindle and interchangeable slides



Application:

For measuring e.g. shank diameters, external dimensions of workpieces etc.

Execution:

- carbide-tipped measuring faces
- Reset
- LOCK function
- mm/inch changeover
- AUTO OFF
- Origin (measurement presetting)
- ABS function
- HOLD (measured value storage)
- TOL (input of tolerances and warning limits)
- EWri-V: MarConnect data output

Advantage:

- Digit height 10 mm
- Non-rotating spindle
- QUICK DRIVE quick adjustment
- Includes 6 pairs of exchangeable gauge slides

Delivery:

incl. operating instructions, battery, case and 1 each of the following gauge slide pairs: 40 Ef planar dia. 6.5 mm, 40 Ea stepped dia. 2 x 4 mm, 40 Et plate dia. 11.3 mm, 40 Eb spherical R=5 mm, 40 Ep tapered 60° 0.3-5.5 mm, 40 Es blade-type 0.75 x 4 mm



| | |
|---|---|
| Art. no. | 31403 586 |
| Brand | MAHR |
| Manufacturer Part Number | 4157150 |
| Min./max. length measuring range | 0-25 mm |
| Digit increment | 0.001 mm |
| Data transmission type | MarConnect |
| Measuring surface diameter | 6.5 mm |
| IP protection class | IP 65 |
| Functions | Reset (Zeroing the display), ABS function, Origin (Dimension preset), Lock-function (Keyboard lock), TOL (Tolerance and warning limits input), Hold-function (AE lock), Data (Data transfer), Bi-directional data interface |
| Number of rechargeable batteries/batteries | 1 PCS |
| Battery designation | 3V CR2032 Lithium |
| Calibration Group | D |
| Gross Weight | 1.200 kg |
| Product Group | 305 |

EAN

4059192058609