

Safety coupling eSafe series 320 – DN 7.6, steel, zinc-plated

In line with ISO 4414 and EN 983



Application:

For connecting hoses to compressed air tools and compressed air machines.

Execution:

- High-performance coupling relieving pressure before uncoupling to eliminate the risk of hose backstroke
- Male threads on the coupling and nipple are factory-fitted with thread seals

Advantage:

- Pressure relief for improved safety
- Very high flow capacity
- Rugged and durable



Art. no.	75135 109
Brand	CEJN
Manufacturer Part Number	103202003
Type	with hose connection
Inner hose diameter	8 mm
Flow capacity	2250 l/min
Max. operating pressure	16 bar
Length	76.5 mm
Width across flats	19 mm
Min./max. temperature resistance	-20 to +100 °C
Gross Weight	0.088 kg
Product Group	7AI

EAN

739139004476 1