

Power Rack Xtreme

CPR16-C2-F7-CB

1x CEE16A In / Daisy chain, 7 x Schuko Typ F Out.

Power Rack Xtreme is a powerful and highly reliable distribution solution for installation in the 19" Rack. It is ideally suited for amplifier rack wiring application.



Features & Benefits

- High quality electrical and electronical component from the renowned brands
- Circuit protection with residual current device (RCCB) and miniature circuit breakers (MCB)
- High quality assembly in EU
- Attractive price / value ratio

Markets & Applications

- Markets: Professional audio esp. amp rack wiring / lighting / video wall
- Mobile applications: Festivals, live events. Control panels / rooms.
- Semi-permanent applications: Theaters, studios, fairs. Control panels /rooms.

Ordering information

Article name	Details	Order code
CPR16-C2-F7-CB	Front: IN 1x CEE16A; Daisy chain 1x CEE16A; OUT 1x Schuko Type F; Circuit protection: 1x RCCB (3-pole + N), 3x MCB (1-pole). Back: OUT 6x Schuko Type F	1028797

Technical Information

Product	
Input device	1x CEE16A 5P red (front)
Daisy chain	1x CEE16A 5P red (daisy chain) front
Output device	7x Schuko socket with lid

Electrical	
Circuit protection	1x RCCB 40/0,03 A (3-pole + N) 3x MCB C16 (1-pole)
Phase control indicator	L1, L2, L3, green
Rated voltage	415 V/AC, 50 Hz
Rated Current	CEE socket: 415 V Link Schuko socket 230V 16A

Mechanical	
Weight	3.8 kg
Type of construction	19" Housing 2 HE, 1.5 TE
Dimensions	483 x 88 x 104 mm (without fittings)

Material	
Housing	Metal
Color	black

Environmental

Protection class	IP20
Temperature range	-5 to +40°C