



## Technical details

Approvals:	CE
Product standard:	EN 60947-5-5;EN ISO 13850
Release type:	Rotational
Actuator:	Pushbutton
Printing symbol:	Pilz logo and E-STOP symbol
Colour button:	Red
Protective collar:	No
Self-monitored:	Yes
Terminal type:	Screw terminal
Number of N/C:	2
Max. current at AC15:	3.0 A
Voltage at AC15:	250 V
Max. current at DC13 I (6 cycles/min):	2.0 A
Voltage at DC13:	24 V
Protection type, housing:	IP65
Mounting type:	Front panel installation
Diameter of mounting cut-out:	22.3 mm
Width dimension:	55.0 mm
Height dimension:	100.0 mm
Gross weight:	79 g

Net weight:

66 g

Ambient temperature:

-30 - 70 °C