

**RMM 11/230 V OUTPUT RELAY**


IN: 230 VAC/DC - OUT: 250 VAC/DC / 6 A


1 relay; 1 NO contact

5 A

230 V AC

Screw terminals

[Link to Product](#)**Illustration**



Product may differ from Image

### Utilization category

AC-12	6 A (24/110/230 V AC)
AC-15	4 A (24/110/230 V AC)
DC-13	2 A (24 V DC); 0.25 A (110 V DC); 0.1 A (230 V DC)

### Input

Connection voltage - current	230 VAC/DC (195...250 VAC/DC) - 3.5mA
LED display	LED (red)

### General data

Mech./ elect. life	20.000.000 switching cycles/load dependent
Test isolation voltage	4 kV
Mounting method	DIN-rail mountable TH35 or G32 (EN 60715)
Temperature range	-20...+50 °C
Dimensions H × W × D	56×12×65 mm

### Output

Switching voltage	max. 250 V AC/300 V DC
Switching current per output	max. 5 A
Min. load current	100 mA
Power rating (voltage dependent)	max. 1250 VA/240 W
Switching frequency	max. 10 Hz
Contact material	Ag Ni 0.15 hv; Ag hv
Energize/release/contact bounce time	10/15/1.5 ms

### Commercial data

country of origin	CZ
customs tariff number	85364900
minimum order quantity	1