

Item code

CDFA 1.5



Brief description:

10A CD contacts, silver plated, 1,50mmq, AWG 16

Product description

| | |
|--------------------|-----------------------------|
| Model | female contacts |
| Version | Crimp contacts CLASS series |
| Series | 10A CD contacts |
| Family | crimp contacts |
| N° of poles | 1 pole |

Technical data

| | |
|---|----------------------|
| Current | 10 A |
| Wire section | 1,50 mm ² |
| AWG size | 16 |
| Operating temperature range (min, max) | -40°C ... +125°C |
| Contact type | silver plated |

Other technical details

| | |
|------------------------------------|------------------------|
| Contact resistance | ≤ 0,3 mΩ |
| Blade size for main contact | 100A: 15mm; 16A: 7,5mm |
| Weight | 0,76 g |

Approvals / Standards

| | |
|---------------------|---|
| Quality mark |  , EAC |
| Conformity | CQC, CE |

General ordering information

| | |
|----------------------|---------------|
| EAN code | 8015747014687 |
| Tariff number | 85369095 |

Packaging Information

| | |
|----------------------------------|----------------------|
| Packaging length | 112,00 mm |
| Packaging height | 95,00 mm |
| Packaging width | 117,00 mm |
| Packaging weight | 1,22 kg |
| Packaging volume | 1,24 dm ³ |
| Packaging description | Carton box |
| Packaging quantity | 1600 Pcs |
| Packaging EAN code | 8015747103992 |
| Sub-packaging length | 50,00 mm |
| Sub-packaging height | 44,00 mm |
| Sub-packaging width | 50,00 mm |
| Sub-packaging weight | 0,15 kg |
| Sub-packaging volume | 0,11 dm ³ |
| Sub-packaging description | Plastic box |
| Sub-packaging quantity | 200 Pcs |
| Sub-packaging EAN barcode | 8015747014694 |



Item code

C DFA 1.5



Catalogue drawings

CDM



CDF