

## Han B Prot.Cover Die Cast for CtoC hood



Image is for illustration purposes only. Please refer to product description.

Part number	09 30 024 5436
Specification	Han B Prot.Cover Die Cast for CtoC hood
HARTING eCatalogue	<a href="https://b2b.harting.com/09300245436">https://b2b.harting.com/09300245436</a>

### Identification

Category	Accessories
Series of hoods/housings	Han <sup>®</sup> B
Type of hood/housing	Protection cover
Description of hood/housing	for cable to cable housing
	Metal With fixing cord
Type	Low construction
	High construction

### Version

Size	24 B
Locking type	Single locking lever

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4
	4X
	12

### Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained



**Pushing Performance**  
Since 1945

## Material properties

REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R1 (HL 1-3) R7 (HL 1-3)

## Specifications and approvals

Approvals	DNV GL
-----------	--------

## Commercial data

Packaging size	1
Net weight	78.9 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140048010
eCl@ss	27440208 Cap for industrial connectors