

Product information

95 77 600

Wire Rope and ACSR-Cable Cutter

IEC 60900 DIN EN 60900

- For wire ropes and steel rods, copper and aluminium cables
- Suitable for cutting overhead cables with strain relief wire (ACSR-cables)
- Angular cutting blades allow cutting of single rope wire
- Optimum transmission ratio for high cutting performance
- Bolted cutter head, replaceable
- Low weight
- Handles: aluminium, high-strength
- Cutter head: high-grade special tool steel, multi stage oil-hardened



⚡ 1000 V

General	
Article No.	95 77 600
EAN	4003773025313
Head	polished
Handles	with dipped insulation
Weight	2,359 g
Dimensions	600 x 230 x 37 mm
Standard	DIN EN 60900 IEC 60900
REACH compliant	contains SVHC
RoHS compliant	not applicable
Technical details	
Cutting capacity copper cable, multiple-stranded	150 mm ²
Cutting capacity copper cable, fine-stranded (diameter)	Ø 14.0 mm
Cutting capacities wire rope (diameter)	Ø 14.0 mm
Cutting capacities medium hard wire (diameter)	Ø 9.0 mm
Cutting capacities iron (diameter)	Ø 9 mm
AWG	6 / 0

technical change and errors excepted

