


ergo[®] Series

Electronic Cutters and Pliers





LINDSTRÖM


483-849 to 483-916





• Ergo design

Part No.	A mm	B mm	C mm	D mm	Type of Cut	Cutting Capacity, mm	$\frac{D}{E}$		
4130	120	9	11	6,8	Micro Flush	0,3-1,5 Cu*	60	3	3
4131	120	9	11	6,8		0,3-1,5 Cu*	60		



*Cu = Copper Wire






Part No.	A mm	B mm	C mm	D mm	G** mm	Type of Cut	Cutting Capacity, mm	$\frac{D}{E}$		
4231	119	12	10	6,8	12,8	Flush Flush	0,3-1,25 Cu*	55	3	3
4238	129	9	9	6,8	6,1		0,3-1,0 Cu*	60		



*Cu = Copper Wire



**45°
**15°






Part No.	A mm	B mm	C mm	D mm	E mm	F mm	Jaw surface	$\frac{D}{E}$		
4430	135	20	9	6,8	1	1	Smooth	65	3	3



Part No.	A mm	B mm	C mm	D mm	E mm	F mm	Jaw surface	$\frac{D}{E}$		
4830	135	20	9	6,8	1	1	Smooth	60	3	3
4833	131,5	22,5	9	6,8	1	1	Smooth Bent to 60°	60	3	3



Part No.	A mm	B mm	C mm	D mm	F mm	$\frac{D}{E}$		
4530	135	20	9	6,8	0,8	60	3	3



SANDVIK
Bahco

AB Sandvik Bahco, S-745 82 Enköping, Sweden.
Phone int. +46 171 22700. Telefax int. +46 171 32237. Telex 40745 Bahtool S.