



### FEATURES:

- Ideal for resistant measurements below 1 ohm.
- Compatible with Fluke and Keithley 4 wire test instruments.
- Four wire measurement using the Kelvin Clip reduces the IR drop in test leads that can cause measurement inaccuracies on 5 ½ and 6 ½ digit DMM's
- Additional banana plug and alligator clip are connected to the shield of the coaxial cables for added shield protection.
- Clamps and banana plugs are color coded for ease of testing.

### MATERIALS:

Banana plugs: Gold plated Beryllium Copper for low contact resistance.

### RATINGS:

Operating Temperature: 50° C.

Operating Voltage: 45 Volts Max.

Current: 5 Amperes Max.

### ORDERING INFORMATION: Model 5940

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).  
All specifications are to the latest revisions. Specifications are subject to change without notice.  
Registered trademarks are the property of their respective companies. Made in USA