

SCLC HSS boring bar, positive right

for face and longitudinal turning using CC indexable insert

ATORN[®]

Application


For copy turning and longitudinal turning using CC indexable insert 80°.

Version

- precision-manufactured **HSS** boring bar, with inner cooling, C type, 95° pitch angle, 80° tip angle, 7° clearance angle

Advantage

- universal use for facing and longitudinal turning
- positive body geometry ensures low cutting forces
- very high rigidity and excellent cutting quality thanks to HSS supporting material



Art. No.	17846 330
ISO name	AH 10 K SCLC R/L 06
Min. bore diameter	12 mm
Shaft diameter	10 mm
Cutting edge height	4.5 mm
Clearance length	20 mm
Length	125 mm
Clamping surface height	9 mm
Programming size	6 mm
Suitable for indexable inserts	CC.. 0602..
Tool design	Right
DIN	8024

EAN-Code

4050293320312