

## Scroll chuck

**ORION®**

### Application:


Suitable for individual or series parts for small workpieces with thin walls as well as for use as a workpiece holder on drilling and grinding machine tables.

### Execution:

- Steel body
- Jaws are case-hardened and reversible
- Ref. no. 010/020 with 3 jaws, ref. no. 040 with 6 jaws.
- Chuck with soft jaws
- Chuck with collet holder or Morse taper shank
- Centric clamping
- See table:
- Clamping range min./max.= internal clamping
- Clamping range 2 min./max. = external clamping

### Delivery:

Chuck JF ultra-flat, incl. a set of reversible, case-hardened interchangeable jaw grips type D



<b>Art. no.</b>	<b>22380 010</b>
<b>Brand</b>	ORION
<b>Manufacturer Part Number</b>	22380010
<b>Number of jaws</b>	3 PCS
<b>Outer diameter</b>	57 mm
<b>Min./max. clamping range 2</b>	1-61 mm
<b>Min./max. clamping range</b>	13-50 mm
<b>Height without jaws</b>	13.8 mm
<b>Clearance hole</b>	8 mm
<b>Gross Weight</b>	0.296 kg
<b>Product Group</b>	220

### EAN

4039247144600